

ACT 100S SERIES MODEL NO. IDENTIFICATION

ACT - 100S - XXX - X - X - X - X - X

ZONES

1 = 1 ZONE
 2 = 2 ZONES
 3 = 3 ZONES*

PRESSURE

H = 75 - 100psi
 L = UNDER 75psi

FILTRATION

130 = 130 MICRON
 100 = 100 MICRON
 055 = 55 MICRON
 025 = 25 MICRON

POWER OPTION

1 = 12Vdc
 2 = 12Vac
 3 = 24Vac

ENCLOSURE


1 = VAULT - GRN
 2 = VAULT - PRL
 3 = RR - GRN
 4 = RR - PRL
 5 = RR/T - GRN
 6 = RR/T - PRL
 7 = RR - NONE

FLOWMETER

A - NONE
 B - STANDARD
 C - FEEDBACK

NOTES:

* ONLY ON VAULT MODELS



DRAWN BY SMS	APPROVED BY JFP	DATE 02/27/06
-----------------	--------------------	------------------

PRODUCTION DRAWING

ACT 100S SERIES SYSTEM ORDERING DESIGNATIONS



1401-B Creek Circle
 BRYAN, TX 77807

979.779.6500

FAX.779.6505

jnm@jnmtechnologies.com

SCALE
 NTS

TOLERANCES UNLESS NOTED	
FRACTIONS	± 1/32
XXXX	± .005
XXX	± .010
XX	± .015
ANLGES	± 1/2"